



Rough / Vibration Service

150A21/RS/VS/BR 120/130V 60PK


Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

Product data

| General Information | |
|--------------------------|-----------------------------------|
| Cap-Base | E26 [Single Contact Medium Screw] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Luminous Flux | 2,205 lm |
| Operating and Electrical | |
| Power Consumption | 150 W |
| Starting Time (Nom) | 0.0 s |
| Voltage (Nom) | 120-130 V |

| Mechanical and Housing | |
|---------------------------------|-------------------------------|
| Bulb Finish | Frosted |
| Bulb Shape | A21 [A 21mm] |
| Product Data | |
| Order product name | 150A21/RS/VS/BR 120/130V 60PK |
| Full product name | 150A21/RS/VS/BR 120/130V 60PK |
| Order code | 275784 |
| Material Nr. (12NC) | 925287435502 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677275785 |
| Numerator - Packs per outer box | 60 |
| EAN/UPC - Case | 50046677275780 |

Dimensional drawing



| Product |
|-------------------------------|
| 150A21/RS/VS/BR 120/130V 60PK |

