



Halogen Classic Candle B35

ClassicHalo 28W B22 240V B35 CL 2PF/10x7

Philips Halogen Classic Candle light bulbs offer the classical shape you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data

| General Information | |
|------------------------|----------------------------------|
| Cap-Base | B22 [B22] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 2,000 h |
| Switching Cycle | 8,000 |
| Rated Lifetime (Hours) | 2,000 h |
| Lighting Technology | Halogen |

| Light Technical | |
|------------------------------------|-----------|
| Luminous Flux | 370 lm |
| Correlated Color Temperature (Nom) | 2800 K |
| Luminous Efficacy (rated) (Nom) | 12.4 lm/W |
| Color rendering index (CRI) | 100 |

| Operating and Electrical | |
|---------------------------|----------------------|
| Power Consumption | 28.0 W |
| Lamp Current (Nom) | 0.12 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 240 V |

| | |
|---------------|-------|
| Voltage (Nom) | 240 V |
|---------------|-------|

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------|--------------|
| Bulb Finish | Clear |
| Bulb Shape | B35 [B 35mm] |

| Approval and Application | |
|-------------------------------|--------|
| Energy Consumption kWh/1000 h | 28 kWh |


| Product Data | |
|---------------------------------|--|
| Order product name | ClassicHalo 28W B22 240V B35 CL 2PF/10x7 |
| Full product name | ClassicHalo 28W B22 240V B35 CL 2PF/10x7 |
| Full product code | 871829121960600 |
| Order code | 925639845505 |
| Material Nr. (12NC) | 925639845505 |
| Local order code | C35CL28W240VBC |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291219606 |
| Numerator - Packs per outer box | 70 |

Halogen Classic Candle B35

EAN/UPC - Case

8718291219620

Dimensional drawing



| Product | D (max) | C (max) |
|--|---------|---------|
| ClassicHalo 28W B22 240V B35 CL 2PF/10x7 | 36 mm | 94.5 mm |

