



Halogen Classic Candle B35

ClassicHalo 28W B22 240V B35 FR 2PF

Philips Halogen Classic Candle light bulbs offer the classical shape you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data

General Information	
Cap-Base	B22 [B22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 h
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 h
Lighting Technology	Halogen

Light Technical	
Luminous Flux	370 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	12.4 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	28.0 W
Lamp Current (Nom)	0.12 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	240 V

Voltage (Nom)	240 V
---------------	-------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35 [B 35mm]


Approval and Application	
Energy Consumption kWh/1000 h	28 kWh

Product Data	
Order product name	ClassicHalo 28W B22 240V B35 FR 2PF
Full product name	ClassicHalo 28W B22 240V B35 FR 2PF
Full product code	871829121963700
Order code	925639945502
Material Nr. (12NC)	925639945502
Local order code	C35FR28W240VBC
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291219637
Numerator - Packs per outer box	70

Halogen Classic Candle B35

EAN/UPC - Case	8718291219651
----------------	---------------

Dimensional drawing



Product	D (max)	C (max)
ClassicHalo 28W B22 240V B35 FR 2PF	36 mm	94.5 mm

