



# Halogen Classic Reflector

## EcoClassic 42W E27 240V R80 25D FR 1CT

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.


### Product data

| General Information                |                                  |
|------------------------------------|----------------------------------|
| Cap-Base                           | E27 [E27]                        |
| Operating Position                 | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime                   | 2,000 hour(s)                    |
| Switching Cycle                    | 8,000                            |
| Rated Lifetime (Hours)             | 2,000 hour(s)                    |
| Lighting Technology                | Halogen                          |
| Light Technical                    |                                  |
| Beam Angle (Nom)                   | 25 degree(s)                     |
| Correlated Color Temperature (Nom) | 2800 K                           |
| Color rendering index (CRI)        | 100                              |
| Operating and Electrical           |                                  |
| Power Consumption                  | 42 W                             |
| Lamp Current (Nom)                 | 0.18 A                           |
| Starting Time (Nom)                | 0.0 s                            |
| Warm-up time to 60% light          | instant full light s             |
| Power Factor (Fraction)            | 1                                |
| Voltage (Nom)                      | 240 V                            |
| Voltage (Nom)                      | 240 V                            |

| Controls and Dimming            |  |
|---------------------------------|--|
| Dimmable                        | Yes                                    |
| Mechanical and Housing          |  |
| Bulb Finish                     | Frosted                                |
| Bulb Shape                      | R80 [R 80mm]                           |
| Product Data                    |  |
| Order product name              | EcoClassic 42W E27 240V R80 25D FR 1CT |
| Full product name               | EcoClassic 42W E27 240V R80 25D FR 1CT |
| Full product code               | 871829112283800                        |
| Order code                      | 925645445502                           |
| Material Nr. (12NC)             | 925645445502                           |
| Numerator - Quantity Per Pack   | 1                                      |
| EAN/UPC - Product/Case          | 8718291122838                          |
| Numerator - Packs per outer box | 10                                     |
| EAN/UPC - Case                  | 8718291122845                          |

# Halogen Classic Reflector

## Dimensional drawing



| Product                                | D (max) | C (max) |
|--|---------|---------|
| EcoClassic 42W E27 240V R80 25D FR 1CT | 81 mm   | 114 mm  |

