



Halogen Classic Candle B35

ClassicHalo 42W E14 240V B35 CL 2PF

Philips Halogen Classic Candle light bulbs offer the classical shape you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.


Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	630 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	15.0 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	42.0 W
Lamp Current (Nom)	0.18 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	240 V
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35 [B 35mm]
Approval and Application	
Energy Consumption kWh/1000 h	42 kWh
Product Data	
Order product name	ClassicHalo 42W E14 240V B35 CL 2PF
Full product name	ClassicHalo 42W E14 240V B35 CL 2PF
Full product code	871829177012100
Order code	925646345504
Material Nr. (12NC)	925646345504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291770121
Numerator - Packs per outer box	70
EAN/UPC - Case	8718291770145

Halogen Classic Candle B35

Dimensional drawing



Product	D (max)	C (max)
ClassicHalo 42W E14 240V B35 CL 2PF	36 mm	99.2 mm

