



# Halogen Classic P45

## Halogen Classic 42WB22 240V P45 1CT/15 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.


### Product data

General Information	
Cap base	B22 [B22]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 h
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 h
Lighting Technology	Halogen
Light Technical	
Luminous Flux	630 lm
Correlated Colour Temperature	2800 K
Luminous efficacy (rated) (nom.)	15.0 lm/W
Colour rendering index (CRI)	100
Operating and Electrical	
Power Consumption	42 W
Lamp current (nom.)	0.18 A
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (nom.)	240 V
Voltage (nom.)	240 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	P45 [P 45 mm]
Product Data	
Order product name	Halogen 42WB22 240V P45 1CT/15 SRP
Full product name	Halogen Classic 42WB22 240V P45 1CT/15 SRP
Full EOC	872790086298002
Order code	86298002
Material no. (12 NC)	925648745503
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8727900862980
Numerator – packs per outer box	15
EAN/UPC - Case	8718696462584

# Halogen Classic P45

## Dimensional drawing



Product	D (max)	C (max)
Halogen 42WB22 240V P45 1CT/15 SRP	46 mm	72.5 mm

