



# Halogen Classic A-shape

## ClassicHalogen53W B22 240V A55 CL 1CT/10

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

### Product data

General Information	
Cap base	B22 [ B22]
Burning Position	UNIVERSAL [ Any/Universal]
Nominal lifetime (nom.)	2000 h
Switching cycle	8000X

Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	850 lm
Lamp Luminous Flux (Nom)	850 lm
Colour Temperature, horizontal (Nom)	2800 K
Lamp Luminous Efficacy EM (Nom)	16.0 lm/W
Colour Rendering Index, horiz (Nom)	100
LLMF at end of nominal lifetime (min.)	80 %

Operating and Electrical	
Power (Rated) (Nom)	53.0 W
Lamp current (nom.)	0.22 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Bulb finish	Clear (CL)


Approval and Application	
Energy efficiency label (EEL)	D
Energy Consumption kWh/1000 h	53 kWh

Luminaire Design Requirements	
Cap base temperature (max.)	130 °C

Product Data	
Full product code	872790089466001
Order product name	ClassicHalogen53W B22 240V A55 CL 1CT/10
EAN/UPC – product	8727900894660
Order code	925693445504
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	925693445504
Net weight (piece)	30.700 g

# Halogen Classic A-shape

## Dimensional drawing



HalClass 53W B22 240V A55 CL

Product	D (max)	C (max)
ClassicHalogen53W B22 240V A55 CL 1CT/10	56 mm	95.5 mm

