



Halogen Deco

BC40BA11/E12/EV/CL 120V 6/2 TP

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar G25 & G16.5 globes, bent and blunt tip candles, and flames. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	540 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	13.5 lm/W
Color rendering index (CRI)	100
LLMF At End Of Nominal Lifetime (Nom)	80 %
Operating and Electrical	
Power Consumption	40 W
Lamp Current (Nom)	0.33 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1

Voltage (Nom)	120 V
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	BA9
Product Data	
Order product name	BC40BA11/E12/EV/CL 120V 6/2 TP
Full product name	BC40BA11/E12/EV/CL 120V 6/2 TP
Order code	925705436301
Material Nr. (12NC)	925705436301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677419189
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677419184

Halogen Deco

Dimensional drawing

Product	D (max)	C (max)
BC40BA11/E12/EV/CL 120V 6/2 TP	35 mm	104 mm

