



Halogen Deco

BC25G16-1/2C/EV/CL 120V 6/2 TP

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar G25 & G16.5 globes, bent and blunt tip candles, and flames. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,500 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,500 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	280 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	95

Operating and Electrical	
Power Consumption	25 W
Lamp Current (Nom)	0.21 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	G16.5 [G16.5]

Product Data	
Order product name	BC25G16-1/2C/EV/CL 120V 6/2 TP
Full product name	BC25G16-1/2C/EV/CL 120V 6/2 TP
Order code	925707536301
Material Nr. (12NC)	925707536301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677420864
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677420869

Halogen Deco

Dimensional drawing

Product	D (max)	C (max)
BC25G16-1/2C/EV/CL 120V 6/2 TP	51 mm	76 mm

