



Halogen Deco

Halogen 40G25/EV/CL 120V 12/1 TP

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar G25 & G16.5 globes, bent and blunt tip candles, and flames. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,500 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,500 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	550 lm
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	95
Operating and Electrical	
Power Consumption	40 W
Lamp Current (Nom)	0.33 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	G25 (G25)
Product Data	
Order product name	40G25/EV/CL 120V 12/1 TP
Full product name	Halogen 40G25/EV/CL 120V 12/1 TP
Order code	420844
Material Nr. (12NC)	925707936301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677420840
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677420845

Halogen Deco

Dimensional drawing

Product	D (max)	C (max)
40G25/EV/CL 120V 12/1 TP	80 mm	115 mm

