



Standard Lustre P45 frosted

Stan 60W E14 230V P45 FR 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base


Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	650 lumen
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45 [P 45mm]
Approval and Application	
Energy Consumption kWh/1000 h	60 kWh
Product Data	
Full product code	871869659045400
Order product name	Stan 60W E14 230V P45 FR 1CT/10X10F
Order code	926000003896
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	926000003896
Full product name	Stan 60W E14 230V P45 FR 1CT/10X10F
EAN/UPC - Case	8718696590478
EAN/UPC - Product/Case	8718696590454

Standard Lustre P45 frosted

Dimensional drawing



Product	D	C (max)
Stan 60W E14 230V P45 FR 1CT/10X10F	45 mm	78 mm

