



# Reflector diam 50 mm

## Refl 25W E14 230V NR50 30D 1CT/30

Reflector lamps based on advanced spotlighting technology


### Product data

| General Information         |                                  |
|-----------------------------|----------------------------------|
| Cap-Base                    | E14 [E14]                        |
| Operating Position          | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime            | 1,000 hour(s)                    |
| Rated Lifetime (Hours)      | 1,000 hour(s)                    |
| Lighting Technology         | Incandescent                     |
| Light Technical             |                                  |
| Beam Angle (Nom)            | 30 degree(s)                     |
| Color rendering index (CRI) | 100                              |
| Operating and Electrical    |                                  |
| Power Consumption           | 25 W                             |
| Voltage (Nom)               | 230 V                            |
| Voltage (Nom)               | 230 V                            |
| Controls and Dimming        |                                  |
| Dimmable                    | Yes                              |

| Mechanical and Housing          |                                   |
|---------------------------------|-----------------------------------|
| Bulb Finish                     | Frosted                           |
| Bulb Shape                      | NR50 [NR 50mm]                    |
| Product Data                    |                                   |
| Order product name              | Refl 25W E14 230V NR50 30D 1CT/30 |
| Full product name               | Refl 25W E14 230V NR50 30D 1CT/30 |
| Full product code               | 871869659078200                   |
| Order code                      | 926000004576                      |
| Material Nr. (12NC)             | 926000004576                      |
| Numerator - Quantity Per Pack   | 1                                 |
| EAN/UPC - Product/Case          | 8718696590782                     |
| Numerator - Packs per outer box | 30                                |
| EAN/UPC - Case                  | 8718696590799                     |

Reflector diam 50 mm

Dimensional drawing



| Product                           | D     |
|-----------------------------------|-------|
| Refl 25W E14 230V NR50 30D 1CT/30 | 50 mm |

Photometric data



Light Distribution Diagram - Refl 25W E14 230V NR50 30D 1CT/30

