



# Standard Lustre P45 clear

## STAN 60W E14 230V P45 CL 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E-base

### Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	650 lm
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]

Product Data	
Order product name	Stan 60W E14 230V P45 CL 1CT/10X10F
Full product name	STAN 60W E14 230V P45 CL 1CT/10X10F
Full product code	871150006699250
Order code	06699250
Material Nr. (12NC)	926000005022
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500066992
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500082268

## Standard Lustre P45 clear

### Dimensional drawing



Product	D	C (max)
Stan 60W E14 230V P45 CL 1CT/10X10F	45 mm	78 mm

