



# Standard Lustre P45 clear

## Stan 60W E27 230V P45 CL 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

### Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	640 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]
Product Data	
Order product name	Stan 60W E27 230V P45 CL 1CT/10X10F
Full product name	Stan 60W E27 230V P45 CL 1CT/10X10F
Full product code	871829174710900
Order code	926000005846
Material Nr. (12NC)	926000005846
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291747109
Numerator - Packs per outer box	100
EAN/UPC - Case	8718291747123

Standard Lustre P45 clear

Dimensional drawing



Product	D	C (max)
Stan 60W E27 230V P45 CL 1CT/10X10F	45 mm	73 mm

