



Standard Lustre P45 frosted

Stan 40W E27 230V P45 FR 1CT/10X10F

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

Product data

| General Information | |
|------------------------|----------------------------------|
| Cap-Base | E27 |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |

| Light Technical | |
|-----------------------------|--------|
| Luminous Flux | 390 lm |
| Color rendering index (CRI) | 100 |

| Operating and Electrical | |
|--------------------------|-------|
| Power Consumption | 40 W |
| Voltage (Nom) | 230 V |
| Voltage (Nom) | 230 V |


| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------|---------|
| Bulb Finish | Frosted |
| Bulb Shape | P45 |

| Product Data | |
|---------------------------------|-------------------------------------|
| Order product name | Stan 40W E27 230V P45 FR 1CT/10X10F |
| Full product name | Stan 40W E27 230V P45 FR 1CT/10X10F |
| Full product code | 871150001122050 |
| Order code | 926000007412 |
| Material Nr. (12NC) | 926000007412 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500011220 |
| Numerator - Packs per outer box | 100 |
| EAN/UPC - Case | 8711500084125 |

Standard Lustre P45 frosted

Dimensional drawing



| Product | D | C (max) |
|-------------------------------------|-------|---------|
| Stan 40W E27 230V P45 FR 1CT/10X10F | 45 mm | 73 mm |

