



Accentline

Accent 50W GU5.3 12V 36D 1CT/10X5F


Low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	36 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	50 W
Lamp Current (Nom)	4.17 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Energy Consumption kWh/1000 h	53 kWh
Product Data	
Order product name	Accent 50W GU5.3 12V 36D 1CT/10X5F
Full product name	Accent 50W GU5.3 12V 36D 1CT/10X5F
Full product code	871150041205800
Order code	926000850034
Material Nr. (12NC)	926000850034
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500412058
Numerator - Packs per outer box	50
EAN/UPC - Case	8718291756033

Dimensional drawing



Product	D (max)	C (max)
Accent 50W GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

