



Accentline

Accent 20W 4000h GU5.3 12V 36D 1CT/10X5F

Low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 hour(s)
Switching Cycle	16,000
Rated Lifetime (Hours)	4,000 hour(s)
Lighting Technology	Halogen
Life to 50% Failures (Nom)	4,000 hour(s)

Light Technical	
Beam Angle (Nom)	36 degree(s)
Luminous Flux	205 lm
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	205 lm

Operating and Electrical	
Power Consumption	20 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	Instant full light s
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]

Approval and Application	
Energy Consumption kWh/1000 h	21 kWh

Product Data	
Order product name	Accent 20W 4000h GU5.3 12V 36D 1CT/10X5F
Full product name	Accent 20W 4000h GU5.3 12V 36D 1CT/10X5F
Full product code	871869658839000
Order code	926000850061
Material Nr. (12NC)	926000850061
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696588390
Numerator - Packs per outer box	50
EAN/UPC - Case	8718696588413

Accentline

Dimensional drawing



Product	D (max)	C (max)
Accent 20W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

