



Double Ended Linear

1500T3Q/CL 277V 12PK

High-quality white light with superior lumen performance. Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.


Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	P4 [Parallel +/-4D or Horizontal(HOR)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	33,000 lumen
Luminous Efficacy (rated) (Nom)	22 lm/W
Operating and Electrical	
Power Consumption	1,500 W
Lamp Current (Nom)	6.25 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	240 V
Voltage (Nom)	240 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3 [T 12mm (T3)]
Product Data	
Order product name	1500T3Q/CL 277V 12PK
Order code	926000850093
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	926000850093
Full product name	1500T3Q/CL 277V 12PK
EAN/UPC - Case	50046677419962
EAN/UPC - Product/Case	046677150396

Double Ended Linear

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
1500T3Q/CL 277V 12PK	12 mm	252.3 mm	250.7 mm	249.1 mm	254.1 mm

