



# MR16

## BC-50MRC16/FL 6/3 TP

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.


### Product data

| General Information                |                                  |
|------------------------------------|----------------------------------|
| Cap-Base                           | GU5.3 [GU5.3]                    |
| Operating Position                 | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime                   | 2,000 hour(s)                    |
| Switching Cycle                    | 8,000                            |
| Rated Lifetime (Hours)             | 2,000 hour(s)                    |
| Lighting Technology                | Halogen                          |
| Light Technical                    |                                  |
| Beam Angle (Nom)                   | 36 degree(s)                     |
| Correlated Color Temperature (Nom) | 3000 K                           |
| Color rendering index (CRI)        | 100                              |
| Operating and Electrical           |                                  |
| Power Consumption                  | 50 W                             |
| Lamp Current (Nom)                 | 4.17 A                           |
| Starting Time (Nom)                | 0.0 s                            |
| Voltage (Nom)                      | 12 V                             |
| Voltage (Nom)                      | 12 V                             |

| Controls and Dimming            |                      |
|---------------------------------|----------------------|
| Dimmable                        | Yes                  |
| Mechanical and Housing          |                      |
| Bulb Shape                      | MR16 [2inch/50mm]    |
| Approval and Application        |                      |
| Energy Consumption kWh/1000 h   | 53 kWh               |
| Product Data                    |                      |
| Order product name              | BC-50MRC16/FL 6/3 TP |
| Full product name               | BC-50MRC16/FL 6/3 TP |
| Order code                      | 926000850099         |
| Material Nr. (12NC)             | 926000850099         |
| Numerator - Quantity Per Pack   | 1                    |
| EAN/UPC - Product/Case          | 046677415808         |
| Numerator - Packs per outer box | 6                    |
| EAN/UPC - Case                  | 50046677415803       |

MR16

Dimensional drawing



| Product              | D (max) | C (max) |
|----------------------|---------|---------|
| BC-50MRC16/FL 6/3 TP | 51 mm   | 46 mm   |

