



Preheat T8

F30T8/CW ALTO 30PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	33
Luminous Flux	2,200 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	62
Operating and Electrical	
Power Consumption	30 W
Mechanical and Housing	
Bulb Shape	T-8 (T8)

Approval and Application	
Mercury (Hg) Content (Nom)	1.9 mg
Product Data	
Order product name	F30T8/CW ALTO 30PK
Full product name	F30T8/CW ALTO 30PK
Order code	281477
Material Nr. (12NC)	927825403326
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677281472
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677281477

Preheat T8

Dimensional drawing

Product
F30T8/CW ALTO 30PK

