



T8 Standard

F17T8/SUPER 84/ALTO 30PK

Philips T8 lamps are energy-efficient lighting solutions.

Product data

| General Information | |
|------------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Features | ALTO® (ALTO) |
| Light Technical | |
| Luminous Flux | 1,275 lm |
| Color Designation | Super 84 |
| Correlated Color Temperature (Nom) | 4100 K |
| Color rendering index (CRI) | 82 |
| Operating and Electrical | |
| Power Consumption | 17 W |
| Mechanical and Housing | |
| Bulb Shape | T-8 (T8) |

| Approval and Application | |
|---------------------------------|--------------------------|
| Energy Saving Product | Energy Saving |
| Mercury (Hg) Content (Nom) | 1.7 mg |
| Product Data | |
| Order product name | F17T8/SUPER 84/ALTO 30PK |
| Full product name | F17T8/SUPER 84/ALTO 30PK |
| Order code | 927842074101 |
| Material Nr. (12NC) | 927842074101 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677427986 |
| Numerator - Packs per outer box | 30 |
| EAN/UPC - Case | 50046677427981 |

T8 Standard

Dimensional drawing

| Product |
|--------------------------|
| F17T8/SUPER 84/ALTO 30PK |

