



Slimline 800 Series T12

F40T12/SUPER 86/ALTO 30PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Luminous Flux	2,800 lumen
Color Designation	Super 86
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	40 W
Mechanical and Housing	
Bulb Shape	T-12 (T12)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F40T12/SUPER 86/ALTO 30PK
Order code	927845076501
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927845076501
Full product name	F40T12/SUPER 86/ALTO 30PK
EAN/UPC - Case	50046677428049
EAN/UPC - Product/Case	046677428044

Slimline 800 Series T12

Dimensional drawing

Product
F40T12/SUPER 86/ALTO 30PK

