



# TuffGuard Coated T8

## F32T8/ADV841/XEW ALTO TG 25W

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

### Warnings and Safety

- All HO lamps recommended for use only in open fixtures.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	Advantage 841 [CCT of 4100K (842)]
Luminous Flux	2,500 lm
Color Designation	Advantage 841
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	25 W
Mechanical and Housing	
Bulb Shape	T-8 (T8)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	F32T8/ADV841/XEW ALTO TG 25W
Full product name	F32T8/ADV841/XEW ALTO TG 25W
Order code	283085
Material Nr. (12NC)	927852384204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677283087
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677283082

# TuffGuard Coated T8

## Dimensional drawing

Product
F32T8/ADV841/XEW ALTO TG 25W

