



U-Bent Rapid Start T8

FB31T8/TL830/ALTO 15/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL830 [CCT of 3000K (830)]
Luminous Flux	2,750 lm
Color Designation	TL830
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	31 W
Mechanical and Housing	
Bulb Shape	T8-1-5/8U [U-bent T 1inch with 1-5/8" leg spacing]

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
Order product name	FB31T8/TL830/ALTO 15/1
Full product name	FB31T8/TL830/ALTO 15/1
Order code	226712
Material Nr. (12NC)	927861283002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677226718
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677226713

U-Bent Rapid Start T8

Dimensional drawing

Product
FB31T8/TL830/ALTO 15/1

