



PL-S 4 Pin

PL-S 11W/840/4P 1CT/25

PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes


Product data

General Information	
Cap-Base	2G7 [2G7]
Life to 50% Failures (Nom)	8,000 h
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	900 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	77 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	11.6 W
Lamp Current (Nom)	0.160 A
Voltage (Nom)	89 V
Voltage (Nom)	89 V

Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	PL-S 11W/840/4P 1CT/25
Full product name	PL-S 11W/840/4P 1CT/25
Full product code	87115002677100
Order code	927867884065
Material Nr. (12NC)	927867884065
Local order code	PLS11W8404P
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500267771
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500267764


PL-S 4 Pin

Dimensional drawing



Product	D (max)	D1 (max)	C (max)
PL-S 11W/840/4P 1CT/25	27.1 mm	10 mm	219.9 mm

Photometric data



Spectral Power Distribution Colour - PL-S 11W/840/4P 1CT/25

