



# Retail Sales T8

## F32T8/HL730/ALTO 30PK

Energy Savings, extra long life, extra low mercury. T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL830 [CCT of 3000K (830)]
Luminous Flux	2,850 lm
Color Designation	TL830
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	32 W
Mechanical and Housing	
Bulb Shape	T-8 (T8)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	F32T8/HL730/ALTO 30PK
Full product name	F32T8/HL730/ALTO 30PK
Order code	453662
Material Nr. (12NC)	927869783012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677453664
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677453669

Dimensional drawing

Product
F32T8/HL730/ALTO 30PK

