



Retail Sales T8

F32T8/TL850 ALTO II 1/10

Energy Savings, extra long life, extra low mercury. T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

| General Information | |
|------------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Features | ALTO® (ALTO) |
| Light Technical | |
| Color Code | TL850 [CCT of 5000K (850)] |
| Luminous Flux | 2,850 lm |
| Color Designation | TL850 |
| Correlated Color Temperature (Nom) | 5000 K |
| Color rendering index (CRI) | 82 |
| Operating and Electrical | |
| Power Consumption | 32 W |
| Mechanical and Housing | |
| Bulb Shape | T-8 (T8) |

| Approval and Application | |
|---------------------------------|--------------------------|
| Energy Saving Product | Energy Saving |
| Mercury (Hg) Content (Nom) | 1.7 mg |
| Product Data | |
| Order product name | F32T8/TL850 ALTO II 1/10 |
| Full product name | F32T8/TL850 ALTO II 1/10 |
| Order code | 205047 |
| Material Nr. (12NC) | 927869785004 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677205041 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 50046677205046 |

Dimensional drawing

| Product |
|--------------------------|
| F32T8/TL850 ALTO II 1/10 |

