



# Retail Sales T8

## F32T8/TL850 ALTO II 1/10

Energy Savings, extra long life, extra low mercury. T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL850 [CCT of 5000K (850)]
Luminous Flux	2,850 lm
Color Designation	TL850
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	32 W
Mechanical and Housing	
Bulb Shape	T-8 (T8)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	F32T8/TL850 ALTO II 1/10
Full product name	F32T8/TL850 ALTO II 1/10
Order code	927869785004
Material Nr. (12NC)	927869785004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677205041
Numerator - Packs per outer box	1
EAN/UPC - Case	50046677205046

Dimensional drawing

Product
F32T8/TL850 ALTO II 1/10

