



PLUS T8 High Output

F96T8/TL841/HO/PL ALTO TG

Philips PLUS T8 High Output 8-foot fluorescent lamps reduce the impact on the environment by offering long life and low mercury.

Product data

General Information	
Cap-Base	R17D [R17d (RDC)]
Features	ALTO® Plus
Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Luminous Flux	8,200 lumen
Color Designation	TL841
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	86 W
Mechanical and Housing	
Bulb Shape	T-8 (T8)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F96T8/TL841/HO/PL ALTO TG
Order code	927874084107
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927874084107
Full product name	F96T8/TL841/HO/PL ALTO TG
EAN/UPC - Case	50046677409123
EAN/UPC - Product/Case	046677409128

PLUS T8 High Output

Dimensional drawing

Product
F96T8/TL841/HO/PL ALTO TG

