



# TL Rapid Start Standard Colours

## TL-RS 20W-ELD-30 30PK

The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.


### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	7,500 hour(s)
Light Technical	
Color Code	750 [CCT of 5000K]
Luminous Flux	1,075 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	66
Operating and Electrical	
Power Consumption	20 W
Lamp Current (Nom)	0.380 A
Voltage (Nom)	60 V
Voltage (Nom)	60 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T12 [38 mm (T12)]
Approval and Application	
Mercury (Hg) Content (Nom)	1.7 mg
Product Data	
Order product name	TL-RS 20W-ELD-30 30PK
Full product name	TL-RS 20W-ELD-30 30PK
Full product code	872790094349800
Order code	927883075903
Material Nr. (12NC)	927883075903
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900943498
Numerator - Packs per outer box	30
EAN/UPC - Case	8727900943504

TL Rapid Start Standard Colours

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-RS 20W-ELD-30 30PK	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

