



Rapid Start T12

F30T12/D/RS ALTO 30PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

| General Information | |
|------------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Features | ALTO® (ALTO) |
| Light Technical | |
| Color Code | 54 |
| Luminous Flux | 1,950 lm |
| Color Designation | Daylight |
| Correlated Color Temperature (Nom) | 6500 K |
| Color rendering index (CRI) | 79 |
| Operating and Electrical | |
| Power Consumption | 30 W |
| Mechanical and Housing | |
| Bulb Shape | T-12 (T12) |

| Approval and Application | |
|---------------------------------|-----------------------|
| Energy Saving Product | Not Applicable |
| Mercury (Hg) Content (Nom) | 4.4 mg |
| Product Data | |
| Order product name | F30T12/D/RS ALTO 30PK |
| Full product name | F30T12/D/RS ALTO 30PK |
| Order code | 376491 |
| Material Nr. (12NC) | 927886005403 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677376499 |
| Numerator - Packs per outer box | 30 |
| EAN/UPC - Case | 50046677376494 |

Rapid Start T12

Dimensional drawing

| Product |
|-----------------------|
| F30T12/D/RS ALTO 30PK |

