



TL Rapid Start Standard Colours

TLRS110W-S84NG 15 PK

The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.

Product data

General Information	
Cap-Base	R17D [R17d (RDC)]
Features	ALTO® (ALTO)
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	9,500 lm
Color Designation	841
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	110 W
Mechanical and Housing	
Bulb Shape	T-12 (T12)

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	TLRS110W-S84NG 15 PK
Full product name	TLRS110W-S84NG 15 PK
Full product code	872790094382500
Order code	927895284106
Material Nr. (12NC)	927895284106
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900943825
Numerator - Packs per outer box	15
EAN/UPC - Case	8727900943832

TL Rapid Start Standard Colours

Dimensional drawing

Product
TLRS110W-S84NG 15 PK



T12 recessed double contact

