



TL Rapid Start Standard Colours

TLRS110W-S85NG 15 PK

The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	7,500 hour(s)
Light Technical	
Color Code	850 [CCT of 5000K]
Luminous Flux	9,350 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	110 W
Lamp Current (Nom)	0.790 A
Voltage (Nom)	153 V
Voltage (Nom)	153 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T12 [38 mm (T12)]
Approval and Application	
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	TLRS110W-S85NG 15 PK
Full product name	TLRS110W-S85NG 15 PK
Full product code	872790094384900
Order code	927895285007
Material Nr. (12NC)	927895285007
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900943849
Numerator - Packs per outer box	15
EAN/UPC - Case	8727900943856

TL Rapid Start Standard Colours

Dimensional drawing



Product	D (max)	C (max)
TLRS110W-S85NG 15 PK	40.5 mm	2,385.3 mm

