



PL-C Cluster 2-Pin Base 15mm Tube

PL-C15mm PL-C 15MM/22W/27 40PK

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information	
Cap-Base	GX32D-2 [GX32d-2]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,200 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	22 W

Mechanical and Housing	
Bulb Shape	PL-C
Approval and Application	
Energy Saving Product	Energy Saving
Product Data	
Order product name	PL-C 15MM/22W/27 40PK
Full product name	PL-C15mm PL-C 15MM/22W/27 40PK
Order code	241687
Material Nr. (12NC)	927897482702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677241681
Numerator - Packs per outer box	40

PL-C Cluster 2-Pin Base 15mm Tube

EAN/UPC - Case	50046677241686
----------------	----------------

Dimensional drawing



Product
PL-C 15MM/22W/27 40PK

