



# PL-C Cluster 2-Pin Base 15mm Tube

## PL-C15mm PL-C 15MM/28W/27 40PK

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data


General Information	
Cap-Base	GX32D-3 [GX32d-3]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,600 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	28 W

Mechanical and Housing	
Bulb Shape	PL-C
Approval and Application	
Energy Saving Product	Energy Saving
Product Data	
Order product name	28W/827 GX32d-3 1CT
Full product name	PL-C15mm PL-C 15MM/28W/27 40PK
Order code	241695
Material Nr. (12NC)	927897882702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677241698
Numerator - Packs per outer box	40

PL-C Cluster 2-Pin Base 15mm Tube

EAN/UPC - Case	50046677241693
----------------	----------------

Dimensional drawing



Product
28W/827 GX32d-3 1CT

