



# PL-S 2 Pin

## PL-S 7W/840/2P 1CT/25

PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.


### Product data

General Information	
Cap-Base	G23 [G23]
Life to 50% Failures (Nom)	8,000 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	405 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	57 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	7.1 W
Lamp Current (Nom)	0.175 A
Voltage (Nom)	46 V
Voltage (Nom)	46 V
Controls and Dimming	
Dimmable	No

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-S 7W/840/2P 1CT/25
Full product name	PL-S 7W/840/2P 1CT/25
Full product code	871150070678200
Order code	927901108465
Material Nr. (12NC)	927901108465
Local order code	PLS7W8402P
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500706782
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500534019


PL-S 2 Pin

Dimensional drawing



Product	D (max)	D1 (max)	C (max)
PL-S 7W/840/2P 1CT/25	27.1 mm	13 mm	135.5 mm

Photometric data



Spectral Power Distribution Colour - PL-S 7W/840/2P 1CT/25

