



# Blue (/52) - PL-L, PL-S

## PL-S 9W/52/2P 1CT/6X10BOX

By emitting light almost entirely within the 400 to 500 nm bandwidth these Medical Therapy Jaundice PL-L lamps have no radiation from the short wave UVB waveband. They are therefore ideal for treating new born babies suffering from hyperbilirubinemia (neonatal jaundice) and Crigler-Najjar Syndrome (CNS). Moreover, the bandwidth of these lamps peak at the most effective treatment wavelength of 450 nm. This highly efficacious phototherapy treatment has eliminated the need for blood transfusions in almost all jaundiced infants. In addition, with the compact format of this PL-L lamp equipment manufacturers have more design freedom in developing their solutions. By emitting a full spectrum of a high color temperature, the PL-L /953 lamps are ideal for treating SAD.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		UV Depreciation at 1000 h	
Cap-Base	G23 [G23]		20 %
Life to 50% Failures (Nom)	8,000 hour(s)	Operating and Electrical	
Useful Life (Nom)	2,000 hour(s)	Power Consumption	8.6 W
Light Technical		Lamp Current (Nom)	0.17 A
Color Code	52	Voltage (Nom)	60 V
Luminous Flux	130 lm	Voltage (Nom)	60 V
Luminous Efficacy (rated) (Nom)	15 lm/W		

Blue (/52) - PL-L, PL-S

Mechanical and Housing	
Bulb Shape	2XT12
Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
Order product name	PL-S 9W/52/2P 1CT/6X10BOX
Full product name	PL-S 9W/52/2P 1CT/6X10BOX


Full product code	871150064471880
Order code	64471880
Material Nr. (12NC)	927901705203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500644718
Numerator - Packs per outer box	60
EAN/UPC - Case	8711500644732

Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-S 9W/52/2P 1CT/6X10BOX	13 mm	28 mm	129 mm	144.5 mm	167.5 mm

Photometric data



Spectral Power Distribution Colour - PL-S 9W/52/2P 1CT/6X10BOX

