



PL-S Blacklight Blue

PL-S 9W BLB/2P 1CT/6X10CC

PL-S Blacklight Blue is a special low-wattage compact fluorescent lamp emitting long wave UV radiation for detection and analysis purposes in archaeology, money checking, forensic science, food industry, medicine, mineralogy, philately as well for special effects in night clubs, discos, theatres and sign lighting. The 2-pin version is designed for operation on electromagnetic gear, the 4-pin version is designed for operation on electronic gear. Both versions are provided with a plug-in/pull-out lamp base.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G23 [G23]
Useful Life (Nom)	3,000 hour(s)
Light Technical	
Color Code	108 [08 lead free glass]
Color Designation	Blacklight Blue
Operating and Electrical	
Power Consumption	8.6 W
Lamp Current (Nom)	0.17 A
Voltage (Nom)	60 V
Voltage (Nom)	60 V


Mechanical and Housing	
Bulb Shape	2XT12
Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg
UV	
UV-A Radiation 100Hr (IEC)	1.65 W
Product Data	
Order product name	PL-S 9W BLB/2P 1CT/6X10CC
Full product name	PL-S 9W BLB/2P 1CT/6X10CC
Full product code	871150095090180
Order code	927901710807
Material Nr. (12NC)	927901710807

PL-S Blacklight Blue

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500950901
Numerator - Packs per outer box	60

EAN/UPC - Case	8711500950925
----------------	---------------

Dimensional drawing



Product	D1 (max)	B (max)
PL-S 9W BLB/2P 1CT/6X10CC	13.0 mm	145.0 mm

