



# PL-S 2 Pin

## PL-S 9W/865/2P 1CT/25

PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.


### Product data

| General Information                |                    |
|------------------------------------|--------------------|
| Cap-Base                           | G23 [G23]          |
| Life to 50% Failures (Nom)         | 8,000 hour(s)      |
| Light Technical                    |                    |
| Color Code                         | 865 [CCT of 6500K] |
| Luminous Flux                      | 600 lm             |
| Color Designation                  | Cool Daylight      |
| Correlated Color Temperature (Nom) | 6500 K             |
| Luminous Efficacy (rated) (Nom)    | 63 lm/W            |
| Color rendering index (CRI)        | 63                 |
| Operating and Electrical           |                    |
| Power Consumption                  | 8.6 W              |
| Lamp Current (Nom)                 | 0.170 A            |
| Voltage (Nom)                      | 60 V               |
| Voltage (Nom)                      | 60 V               |

| Controls and Dimming            |                       |
|---------------------------------|-----------------------|
| Dimmable                        | No                    |
| Approval and Application        |                       |
| Mercury (Hg) Content (Nom)      | 1.4 mg                |
| Product Data                    |                       |
| Order product name              | PL-S 9W/865/2P 1CT/25 |
| Full product name               | PL-S 9W/865/2P 1CT/25 |
| Full product code               | 871150063506800       |
| Order code                      | 927901786565          |
| Material Nr. (12NC)             | 927901786565          |
| Numerator - Quantity Per Pack   | 1                     |
| EAN/UPC - Product/Case          | 8711500635068         |
| Numerator - Packs per outer box | 25                    |
| EAN/UPC - Case                  | 8711500534057         |

PL-S 2 Pin

Dimensional drawing



| Product               | D (max) | D1 (max) | C (max)  |
|-----------------------|---------|----------|----------|
| PL-S 9W/865/2P 1CT/25 | 27.1 mm | 13 mm    | 167.5 mm |

