



PL-S 2 Pin

PL-S 11W/840/2P 1CT/25

PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.


产品数据

一般信息	
底盖	G23 [G23]
50% 故障条件下的使用寿命 (标称)	8,000 小时
灯技术	
颜色代码	840 [CCT of 4000K]
光通量	900 lm
颜色名称	冷白色 (CW)
相关色温 (标称)	4000 K
光效 (额定)(标称)	77 lm/W
显色指数 (CRI)	82
操作和电气	
功耗	11.6 W
灯具电流 (标称)	0.160 A
电压 (标称)	89 V
电压 (标称)	89 V

控制和调光	
可调光	否
审批和申请	
汞 (Hg) 含量 (标称)	1.4 mg
产品数据	
订单产品名称	PL-S 11W/840/2P 1CT/25
完整的产品名称	PL-S 11W/840/2P 1CT/25
完整产品代码	692341076140500
订购代码	927902308403
材料编号 (12NC)	927902308403
计算器 - 每包数量	1
EAN/UPC - 产品/箱	6923410761405
计算器 - 每个外包装箱中的包数	25
EAN/UPC - 案例	6923410762440


PL-S 2 Pin

二维绘图



Product	D (max)	D1 (max)	C (max)
PL-S 11W/840/2P 1CT/25	27.1 mm	13 mm	236.3 mm

光度数据



Spectral Power Distribution Colour - PL-S 11W/840/2P 1CT/25

