



# PL-S 2 Pin

## PL-S 11W/865/2P 1CT/25

PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.


### Product data

General Information	
Cap-Base	G23 [G23]
Life to 50% Failures (Nom)	8,000 hour(s)
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	900 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	72 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	11.6 W
Lamp Current (Nom)	0.160 A
Voltage (Nom)	89 V
Voltage (Nom)	89 V

Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-S 11W/865/2P 1CT/25
Full product name	PL-S 11W/865/2P 1CT/25
Full product code	871150063510500
Order code	927902386565
Material Nr. (12NC)	927902386565
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500635105
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500534088

PL-S 2 Pin

Dimensional drawing



Product	D (max)	D1 (max)	C (max)
PL-S 11W/865/2P 1CT/25	27.1 mm	13 mm	236.3 mm

