



# Actinic BL PL-S/PL-L

## PL-L 18W/10/4P 1CT/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

### 安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### 产品数据

| 一般信息                  |             |
|-----------------------|-------------|
| 底盖                    | 2G11 [2G11] |
| 50% 故障条件下的使用寿命 ( 标称 ) | 15,000 小时   |
| 有效寿命 ( 标称 )           | 5,000 小时    |
| 灯技术                   |             |
| 颜色代码                  | 10          |
| 颜色名称                  | 紫外光 A       |
| 色度坐标 X ( 标称 )         | 228         |
| 色度坐标 Y ( 标称 )         | 215         |
| 2000 小时时的 UV 衰减       | 20 %        |
| 5000 小时时的 UV 衰减       | 35 %        |
| 操作和电气                 |             |
| 功耗                    | 18 W        |


| 灯具电流 ( 标称 )           | 0.375 A               |
|-----------------------|-----------------------|
| 电压 ( 标称 )             | 58 V                  |
| 电压 ( 标称 )             | 58 V                  |
| 机械和外壳                 |                       |
| 灯泡外形                  | 2xT16                 |
| UV                    |                       |
| 紫外光 A 辐射 100 小时 (IEC) | 3.5 W                 |
| 产品数据                  |                       |
| 订单产品名称                | PL-L 18W/10/4P 1CT/25 |
| 完整的产品名称               | PL-L 18W/10/4P 1CT/25 |
| 完整产品代码                | 871150026018540       |
| 订购代码                  | 927903001007          |

Actinic BL PL-S/PL-L

|                  |               |
|------------------|---------------|
| 材料编号 (12NC)      | 927903001007  |
| 计算器 - 每包数量       | 1             |
| EAN/UPC - 产品/箱   | 8711500260185 |
| 计算器 - 每个外包装箱中的包数 | 25            |


|              |               |
|--------------|---------------|
| EAN/UPC - 案例 | 8711500260192 |
|--------------|---------------|

二维绘图



| Product               | D1 (max) | D (max) | A (max)  | B (max) | C (max)  |
|-----------------------|----------|---------|----------|---------|----------|
| PL-L 18W/10/4P 1CT/25 | 18 mm    | 39 mm   | 194.2 mm | 220 mm  | 226.6 mm |

光度数据



Spectral Power Distribution Colour - PL-L 18W/10/4P 1CT/25

