



# MASTER PL-L 4 Pin



## MASTER PL-L 18W/830/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	2G11 [2G11]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	15,000 h
Light Technical	
Colour Code	830 [CCT of 3000K]
Luminous Flux	1,200 lm
Colour designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	67 lm/W
Colour rendering index (CRI)	82
Operating and Electrical	
Power Consumption	18.0 W


Lamp current (nom.)	0.375 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	2 mg
Mercury (Hg) content (nom.)	2.0 mg
Energy consumption kWh/1,000 hours	18 kWh
EPREL registration number	423262
Product Data	
Order product name	MASTER PL-L 18W/830/4P 1CT/25
Full product name	MASTER PL-L 18W/830/4P 1CT/25
Full EOC	871150070668340
Order code	70668340

MASTER PL-L 4 Pin

Material no. (12 NC)	927903008370
Local order code	18PLL830
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500706683


Numerator – packs per outer box	25
EAN/UPC – Case	8711500710734

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 18W/830/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 18W/830/4P 1CT/25

