



MASTER PL-L 4 针

MASTER PL-L 24W/865/4P 1CT/25

紧凑型节能荧光灯。紧凑的长弧结构，低压低汞荧光灯管。由 2 根平行的细荧光灯管组成

安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	2G11 [2G11]
光通量测量参考	Sphere
50% 故障条件下的使用寿命 (标称)	15,000 小时
灯技术	
颜色代码	865 [CCT of 6500K]
光通量	1,750 lm
颜色名称	冷日光
色度坐标 X (标称)	0.313
色度坐标 Y (标称)	0.337
相关色温 (标称)	6500 K
光效 (额定) (标称)	73 lm/W
显色指数 (CRI)	80
操作和电气	
功耗	24.2 W


灯具电流 (标称)	0.345 A
控制和调光	
可调光	是
审批和申请	
能效等级	G
汞 (Hg) 含量 (最高)	2 mg
汞 (Hg) 含量 (标称)	2.0 mg
能耗 kWh/1000 h	25 kWh
EPREL 注册号	423268
产品数据	
订单产品名称	MASTER PL-L 24W/865/4P 1CT/25
完整的产品名称	MASTER PL-L 24W/865/4P 1CT/25
完整产品代码	871150063517440
订购代码	927903286570
材料编号 (12NC)	927903286570

MASTER PL-L 4 针

计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500635174
计算器 - 每个外包装箱中的包数	25


EAN/UPC - 案例	8711500635181
--------------	---------------

二维绘图



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 24W/865/4P 1CT/25	39.0 mm	18.0 mm	289.2 mm	315 mm	321.6 mm

光度数据



Spectral Power Distribution Colour - MASTER PL-L 24W/865/4P 1CT/25

