



MASTER PL-L 4 Pin

MASTER PL-L 36W/830/4P 1CT/25

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	2G11 [2G11]	Power Consumption	36 W
Life to 50% Failures (Nom)	15,000 hour(s)	Lamp Current (Nom)	0.435 A
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	2,900 lumen	Approval and Application	
Color Designation	Warm White (WW)	Mercury (Hg) Content (Nom)	2.0 mg
Correlated Color Temperature (Nom)	3000 K	Energy Consumption kWh/1000 h	40 kWh
Luminous Efficacy (rated) (Nom)	81 lm/W		
Color rendering index (CRI)	>80		

MASTER PL-L 4 Pin

Product Data	
Full product code	87115007067441
Order product name	MASTER PL-L 36W/830/4P 1CT/25
Order code	927903408372
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25


Material Nr. (12NC)	927903408372
Full product name	MASTER PL-L 36W/830/4P 1CT/25
EAN/UPC - Case	8711500710888
EAN/UPC - Product/Case	8711500706744

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 36W/830/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 36W/830/4P 1CT/25

