



MASTER PL-C 2 Pin

MASTER PL-C 10W/840/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | |
|------------------------------------|--------------------|
| Cap-Base | G24D-1 [G24d-1] |
| Life to 50% Failures (Nom) | 10,000 hour(s) |
| Light Technical | |
| Color Code | 840 [CCT of 4000K] |
| Luminous Flux | 600 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 60 lm/W |
| Color rendering index (CRI) | 82 |
| Operating and Electrical | |
| Power Consumption | 10.0 W |
| Lamp Current (Nom) | 0.190 A |

| Controls and Dimming | |
|-------------------------------|------------------------------------|
| Dimmable | No |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 1.4 mg |
| Energy Consumption kWh/1000 h | 13 kWh |
| Product Data | |
| Order product name | MASTER PL-C 10W/840/2P 1CT/5X10BOX |
| Full product name | MASTER PL-C 10W/840/2P 1CT/5X10BOX |
| Full product code | 871150070498600 |
| Order code | 927903884002 |
| Material Nr. (12NC) | 927903884002 |
| Local order code | PLC10W8402P |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500704986 |

MASTER PL-C 2 Pin


| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 50 |
| EAN/UPC - Case | 8711500733047 |

Dimensional drawing




| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|--|---------|----------|---------|---------|----------|
| MASTER PL-C 10W/840/2P 1CT/ 5X10BOX | 27.1 mm | 27.1 mm | 75.5 mm | 95.0 mm | 117.4 mm |

Photometric data




Spectral Power Distribution Colour - MASTER PL-C 10W/840/2P 1CT/5X10BOX

Lifetime



Life Expectancy Diagram - MASTER PL-C 10W/840/2P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 10W/840/2P 1CT/5X10BOX

MASTER PL-C 2 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-C 10W/840/2P 1CT/5X10BOX

