



# MASTER PL-C 2 Pin

## MASTER PL-C 13W/830/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

### Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information	
Cap-Base	G24D-1 [G24d-1]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	925 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	69 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	13.4 W
Lamp Current (Nom)	0.170 A

Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	17 kWh
Product Data	
Order product name	MASTER PL-C 13W/830/2P 1CT/5X10BOX
Full product name	MASTER PL-C 13W/830/2P 1CT/5X10BOX
Full product code	871150026922500
Order code	927904883001
Material Nr. (12NC)	927904883001
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500269225
Numerator - Packs per outer box	50

MASTER PL-C 2 Pin


EAN/UPC - Case	8711500269164
----------------	---------------

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/830/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-C 13W/830/2P 1CT/5X10BOX

Lifetime




Life Expectancy Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX

MASTER PL-C 2 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX

