



MASTER PL-C 2 Pin

MASTER PL-C 13W/830/2P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	G24d-1	Power Consumption	13.4 W
Life to 50% Failures (Nom)	10,000 hour(s)	Lamp Current (Nom)	0.170 A
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	No
Luminous Flux	925 lm	Approval and Application	
Color Designation	Warm White (WW)	Mercury (Hg) Content (Nom)	1.4 mg
Correlated Color Temperature (Nom)	3000 K	Energy Consumption kWh/1000 h	17 kWh
Luminous Efficacy (rated) (Nom)	69 lm/W		
Color rendering index (CRI)	82		

MASTER PL-C 2 Pin

Product Data	
Order product name	MASTER PL-C 13W/830/2P 1CT/5X10BOX
Full product name	MASTER PL-C 13W/830/2P 1CT/5X10BOX
Full product code	871150026922500
Order code	927904883001
Material Nr. (12NC)	927904883001


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500269225
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500269164

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/830/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-C 13W/830/2P 1CT/5X10BOX

Lifetime



Life Expectancy Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX

MASTER PL-C 2 Pin

Lifetime

Life Expectancy Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX

