



# MASTER PL-C 2 Pin

## MASTER PL-C 13W/830/2P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	G24D-1 [G24d-1]	69 lm/W	
Flux measurement reference	Sphere	Color rendering index (CRI)	
Life to 50% Failures (Nom)	10,000 hour(s)	82	
Light Technical		Operating and Electrical	
Color Code	830 [CCT of 3000K]	Power Consumption	13.8 W
Luminous Flux	925 lm	Lamp Current (Nom)	0.170 A
Color Designation	Warm White (WW)	Controls and Dimming	
Chromaticity Coordinate X (Nom)	0.44	Dimmable	No
Chromaticity Coordinate Y (Nom)	0.403	Approval and Application	
Correlated Color Temperature (Nom)	3000 K	Energy Efficiency Class	G

MASTER PL-C 2 Pin


Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	14 kWh
EPREL Registration Number	423279

Product Data

Order product name	MASTER PL-C 13W/830/2P 1CT/5X10BOX
Full product name	MASTER PL-C 13W/830/2P 1CT/5X10BOX
Full product code	871150062084270


Order code	62084270
Material Nr. (12NC)	927904883040
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500620842
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500715685

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/830/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm


Photometric data




Spectral Power Distribution Colour – MASTER PL-C 13W/830/2P 1CT/5X10BOX

MASTER PL-C 2 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX

Lumen Maintenance Diagram - MASTER PL-C 13W/830/2P 1CT/5X10BOX

