



MASTER PL-C 2 Pin

MASTER PL-C 13W/865/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Warnings and Safety

- Use only with electromagnetic control gear
- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Color rendering index (CRI)	
Cap-Base	G24d-1		80
Life to 50% Failures (Nom)	10,000 hour(s)	Operating and Electrical	
		Power Consumption	13.4 W
		Lamp Current (Nom)	0.170 A
Light Technical		Controls and Dimming	
Color Code	865 [CCT of 6500K]	Dimmable	No
Luminous Flux	845 lm		
Color Designation	Cool Daylight		
Correlated Color Temperature (Nom)	6500 K		
Luminous Efficacy (rated) (Nom)	63 lm/W		

MASTER PL-C 2 Pin

Approval and Application


Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	17 kWh

Product Data

Order product name	MASTER PL-C 13W/865/2P 1CT/5X10BOX
Full product name	MASTER PL-C 13W/865/2P 1CT/5X10BOX
Full product code	871150063523500


Order code	927904886502
Material Nr. (12NC)	927904886502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500635235
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500635259

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/865/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm



Photometric data



Spectral Power Distribution Colour - MASTER PL-C 13W/865/2P 1CT/5X10BOX

MASTER PL-C 2 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-C 13W/865/2P 1CT/5X10BOX

Lumen Maintenance Diagram - MASTER PL-C 13W/865/2P 1CT/5X10BOX

Life Expectancy Diagram - MASTER PL-C 13W/865/2P 1CT/5X10BOX

